


97 54 24

Crimping Pliers for micro plugs parallel crimping



- Parallel crimping performance to satisfy the particularly high standards of small connectors
- Repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- Fixed locator for D-Sub micro plugs for an exact positioning of connector and cable
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Crimping pliers for other mini plugs such as HD 22, Modu IV, Micro Timer, MQS ... on request
- Chrome vanadium electric steel in special quality, oil-hardened

Article No.	97 54 24
EAN	4003773060215
Pliers	burnished
Handles	with multi-component grips
Applications	D Sub; HD 20; HDE plug
Capacity in square millimetres mm²	0,03 - 0,56
Number of crimping positions	3
AWG	32 - 20
Length mm	190
Net weight g	305



technical change and errors excepted

