

98 20 40 SL

Screwdriver (Slim) for slotted screws



- Reduced blade isolation diameter for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

Article No.	98 20 40 SL
EAN	4003773079729
Tip	burnished
Handle	insulating multi-component handle, VDE-tested
Blade width mm	4,0
Blade length mm	100
Handle length mm	102
Nominal size	4,0 mm
Blade thickness mm	0,8
Length of non-insulated blade mm	15
Length mm	202
Net weight g	38

technical change and errors excepted