

# PRAKTICA

## Luxmedia Z360

4K Video

3840p

20.0  
Megapixels

Wireless  
Photo  
Sharing



The PRAKTICA Luxmedia Z360 immerses you in the world of 360° content; Shoot 4K videos, take exceptionally detailed photos or live stream on social media all at the push of a button.

Featuring two 180° fisheye lenses and a 20MP sensor, the Z360 effortlessly captures details you never thought possible. It's perfectly pocket-sized and lightweight, making it the ultimate travel essential.

Lose yourself in the world of 360° content. It's a great way to relive your special moments.



### Key Features

- Effortlessly shoot 360° 4K Video
- Capture 360° photos at the touch of a button
- Wirelessly share content via the Pocket360 App
- Live stream on popular social media sites
- Pocket sized thanks to compact design
- Lightweight; only 75g
- Micro USB charging
- Micro SD Card u1/u3 up to 256GB
- Accessories: Micro USB Cable, Quick Start Guide (EN), Hand Strap, Attachment for Strap, Carry Bag

Specification		Graphite: Z360-GY	
Image Resolution	20 Megapixels	Microphone/Speaker	Stereo/Built-in
Image Sensor	1/2.3"	ISO Sensitivity	Up to 3200
Total Pixel	5352(H)x3950(V)	USB	Type B/USB 2.0
Focal Length	40cm ~ Infinity	Power Source	Li-ion (680mAh)
Photo Format	JPEG	Dimensions	35.2x96.5x16.05mm
Video Format	MP4	Weight	75g
Video Resolution	4K@30fps/FHD@30fps		

# PRAKTICA

## Z360 Specification

Image Sensor	1/2.3"
Effective Pixels	5256(H)x3934(V) approx. 20.68 Megapixels
Total Pixel	5352(H)x3950(V) approx. 21.14 Megapixels
Lens Type	Fixed focus, Fisheye
FOV	190° x 2
Focal Length	40cm ~ Infinity
Image Circle	4.373mm
Aperture	F2.0
Display	OLED 0.5"
Microphone	Stereo/Built in
Battery	Li-ion
Battery Capacity	680mAh
Battery Life	130 photos/4K Video - 45 mins/FHD Video - 70 mins
USB	Micro USB Type B/USB 2.0
Storage	Micro SD Card u1/u3 up to 256GB
Image Size	7008x3504/3840x1920/1920x960
Time Lapse	5 sec/10 sec/ 30 sec/60 sec
Electronic Shutter	Still; 1/8000 ~ 1/4 sec / Video; 1/12000 ~ 1/30s
Function Mode	Broadcast/Take picture/Video/Timelapse
White Balance	Auto White Balance
ISO	Auto (Max. ISO 3200)
EV Compensation	0EV, -2~ +2 EV
Image File Format	JPEG
Video Recording	4K - 3840 (H) x1920 (V) @30fps/ FHD - 1920 (H) x960 (V) @30fps Max. Recording Time 1GB File Size
System Requirements	Mac OS 10.8+/ Windows 7, 8, 10
Android Version	5.0+
iOS Version	10.0+
Waterproof	IP54
Shockproof	1m
Operating Temp	0°C ~ 40°C
Operating Relative Humidity	≤85%
Dimensions	35.2x96.5x16.05mm
Weight	75g
Accessories	Micro USB Cable, Quick Start Guide (EN), Hand Strap, Attachment for Strap, Carry Bag

