




Suppliers of Quality Assured Cables

UL/CSA Hook-Up Wire

UL Style 1007/1569

CSA TR-64



Product Type:
UL Cable

Application:
These single core cables are mainly used in the internal wiring of electrical and electronic equipment. They are manufactured and approved to UL and CSA specifications

Standards / Conformances:
UL Style 1007 / 1569
CSA TR-64
Vertical flame propagation: complies with CSA FT-1; UL VW-1.
REACH and RoHS Compliant

Construction:

Conductor:	Tinned annealed copper to UL Subject 758 : CSA Standard C22.2 No.127
Insulation:	PVC compound meeting the requirements of: <ul style="list-style-type: none"> • PVC Class 43 to UL Subject 1581 • Class 19 to CSA Standard C22.2 No. 127

Electrical Characteristics:
Rated Voltage 300V
Temperature rating -10°C to 105°C, (90°C for CSA)

Physical Characteristics:

Product Code	Conductor Size (AWG)	Colour	Length m	Nominal Diameter (mm)	Weight (Kg/Km)
6007345	24	Brown	305	1.45	4.2
6009796	24	Red	305	1.45	4.2
6012451	24	Violet	305	1.45	4.2
6009630	22	Black	305	1.60	5.5
6010897	22	Yellow	305	1.60	5.5
6009933	22	Yellow	100	1.60	5.5
6007683	20	Grey	305	1.70	7.2
6009875	20	Black	305	1.70	7.2
6012452	20	Pink	305	1.70	7.2
6012296	18	White	305	2.0	10.4
6012450	18	Brown	305	2.0	10.4