

# PIXMA TS5150

# SIMPLE AFFORDABLE FAMILY PRINTING WITH SMART CONNECTIVITY



Fun and affordable, this small, stylish family printer takes all the hassle out of creating beautiful borderless images and documents at home with smart wireless connectivity to your devices and the cloud.



- Connect to smart devices via range of options including Bluetooth® for easy Wi-Fi print and scan via Canon PRINT app
- Experience the freedom to print from social media and scan to the cloud\*\* with PIXMA Cloud Link
- Print more pages and save using optional XL FINE ink cartridges and auto 2-sided printing
- Control, view and connect with ease using easy access buttons and 6.2 cm colour screen
- Small, stylish and affordable All-In-One for high quality colour printing, copying and scanning at home

\*Equipped with Bluetooth® low energy technology (Bluetooth print and scan is only available on Android devices). The functions available with Bluetooth communication and the Canon PRINT Inkjet/SELPHY app are not guaranteed on all Android smartphones. The Bluetooth® word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by Canon Inc. is under license. Other trademarks and trade names are those of their respective owners.

\*\*Scan to cloud is only available to genuine Canon ink users.



## Product Range



PIXMA TS8150 Series



PIXMA TS6150 Series



PIXMA TS5150 Series

PIXMA TS9150 Series  
PIXMA TS8150 Series  
PIXMA TS6150 Series  
**PIXMA TS5150 Series**

# TECHNICAL SPECIFICATIONS

# PIXMA TS5150

## GENERAL SPECIFICATIONS

<b>Functions</b>	Wi-Fi, Print, Copy, Scan, Cloud
<b>PRINTER SPECIFICATIONS</b>	
<b>Print Resolution</b>	Up to 4800 <sup>[1]</sup> x 1200 dpi
<b>Print Technology</b>	2 FINE Cartridges (Black and Colour)
<b>Mono Print Speed</b>	Approx. 13.0 ipm <sup>[2]</sup>
<b>Colour Print Speed</b>	Approx. 6.8 ipm <sup>[2]</sup>
<b>Photo Print Speed</b>	Borderless 10 x 15cm : Approx. 43 seconds <sup>[2]</sup>
<b>Borderless Printing</b>	Yes (A4, Letter, 20 x 25cm, 13 x 18cm, 10 x 15cm, 13 x 13cm)
<b>Two Sided Printing</b>	Auto Duplex Print (A4, A5, B5, Letter - plain paper)
<b>CARTRIDGES AND YIELDS</b>	
<b>Standard Ink Cartridges</b>	PG-540 (Black) CL-541 (Colour)
<b>Optional XL Ink Cartridges</b>	PG-540XL (Black) CL-541XL (Colour)
<b>Cartridge Yield (Plain paper)</b>	A4 colour documents printing <sup>[3]</sup> Black: 180 pages Black XL: 600 pages Colour: 180 pages Colour XL: 400 pages
<b>Cartridge Yield (Photo print)</b>	10x15cm colour photo printing <sup>[3]</sup> Black: 2465* photos Black XL: 7560* photos Colour: 69 photos Colour XL: 150 photos * Estimated supplemental yield
<b>PAPER SUPPORT</b>	
<b>Paper Types</b>	Plain Paper Canon High Resolution Paper (HR-101N) Canon Pro Platinum (PT-101) Canon Plus Glossy II (PP-201) Canon Pro Luster (LU-101) Canon Plus Semi-gloss (SG-201) Canon "Everyday Use" (GP-501) Canon Matte (MP-101) Envelopes
<b>Maximum Paper Input</b>	Rear Tray: Max. 20 sheets (photo paper) Front Cassette: Max. 100 sheets (plain paper)
<b>Paper Sizes</b>	Rear Tray: A4/A5/B5/LTR/LGL/20 x 25cm/ 13 x 18cm/10 x 15cm /13 x 13, Envelopes (DL, COM10)
<b>Paper Weight</b>	Front Cassette: A4, A5, B5, LTR Rear Tray: Plain paper 64 - 105 g/m <sup>2</sup> , Canon photo paper up to 300 g/m <sup>2</sup> Front Cassette: Plain Paper: 64-105 g/m <sup>2</sup>

## SCANNER SPECIFICATIONS

<b>Scanner Type</b>	CIS flatbed photo and document scanner
<b>Scanner Resolution (Optical)</b>	1200 x 2400 dpi <sup>[4]</sup>
<b>A4 Scan Speed</b>	Approx. 14 sec <sup>[5]</sup>
<b>Scanning Depth (Input / Output)</b>	Colour: RGB each 16bit/8bit Greyscale: 16 bit / 8 bit
<b>Maximum Document Size</b>	216 x 297 mm

## COPIER SPECIFICATIONS

<b>Copy Speed</b>	sFCOT: Approx. 20sec <sup>[6]</sup> sESAT: Approx. 4.0ipm <sup>[6]</sup> 99 copies max.
<b>Multiple Copy</b>	Document Copying, Photo Copying, Borderless copy, 2-sided copy, 2-on-1 and 4-on-1 copy, Frame erase copy, ID copy
<b>Copy Functions</b>	25 - 400% (in 1% increments) Fit to page A5 to A4, B5 to A4, A4 to A5 and A4 to B5
<b>Copy Zoom</b>	

## INTERFACE

<b>Display Type &amp; Size</b>	6.2cm LCD (TFT colour)
<b>Display Languages</b>	33 Languages Selectable: Japanese/ English(mm & inch)/German/French/Italian/ Spanish/Dutch/Portuguese/Norwegian/Swedish/ Danish/Finnish/Russian/Czech/Hungarian/Polish/ Slovene/Turkish/Greek/Simplified Chinese/ Traditional Chinese/Korean/Indonesian/Slovakian/ Estonian/Latvian/Lithuanian/Ukrainian/Romanian/ Bulgarian/Thai/Croatian/Vietnamese
<b>Interface Type - PC / Mac</b>	Hi-Speed USB (B Port) Wi-Fi: IEEE802.11 b/g/n Wi-Fi Security: WPA-PSK, WPA2-PSK, WEP, Administration password Wireless LAN Frequency Band: 2.4GHz
<b>Interface Type - Other</b>	Bluetooth Low Energy (BLE) Message In Print app PIXMA Cloud Link Canon PRINT Inkjet/SELPHY app Canon Print Service Plugin (Android) Google Cloud Print Apple AirPrint Wireless Direct Access Point Mode WLAN PicBridge Mopria (Android)

# TECHNICAL SPECIFICATIONS

# PIXMA TS5150

## SOFTWARE

### Supported Operating Systems

Windows 10, Windows 8.1, Windows 7 SP1  
Note: For Windows, .NET Framework 4.5.2 or 4.6 is required

### Supported Mobile Systems

OS X 10.10.5–OS X 10.11, macOS 10.12

### Minimum System Requirements

iOS, Android, Windows 10 Mobile  
Windows: 3.1GB disk space, Internet Explorer 8  
Mac: Internet connection, 1.5GB disk space, Safari 5  
Display: 1024 x 768 XGA

### Software Included

MP Driver including Scanning Utility  
My Image Garden with Full HD Movie Print<sup>[7]</sup>  
Quick Menu  
Easy-WebPrint EX (download)<sup>[8]</sup>

## PHYSICAL FEATURES

### Weight

approx. 6.5 kg

### Dimensions (W x D x H)

approx. 425 x 315 x 147mm

### Acoustic Noise Levels

approx. 43.5(A)<sup>[9]</sup>

### Recommended Operating Environment

Temperature: 15-30°C  
Humidity: 10-80% RH (no dew condensation)

### Power Source

AC 100-240V, 50/60Hz

### Power Consumption

Off: Approx. 0.2W  
Standby (connected to PC via USB): Approx. 0.7W (scanning lamp off)  
Standby (all ports connected): Approx. 1.5W (scanning lamp is off)  
Time to enter Standby mode: 11 minutes  
Copying: Approx. 1.4W<sup>[10]</sup>

## Footnotes

<sup>[1]</sup> Ink droplets can be placed with a minimum pitch of 1/4800 inch

<sup>[2]</sup> Document print speeds are the averages of ESAT in Office Category Test for the default simplex mode, ISO/IEC 24734.

Photo print speed is based on the default setting using ISO/JIS-SCID N2 on Photo Paper Plus Glossy II and does not take into account data processing time on host computer.

<sup>[3]</sup> A4 colour documents printing - Declared yield value in accordance with ISO/IEC 24711 standard. Values obtained by continuous printing.

10x15cm colour photo printing - Declared yield value in accordance with ISO/IEC 29102. Values obtained by continuous printing.

<sup>[4]</sup> Optical resolution is a measure of maximum hardware sampling resolution, based on ISO 14473 standard.

<sup>[5]</sup> Color document scan speed is measured with ISO/IEC 29183 Target A.

Scan speed indicates the time measured between pressing the scan button of the scanner driver and the on-screen status display turns off.

Scan speed may vary depending on system configuration, interface, software, scan mode settings and document size etc.

<sup>[6]</sup> Copy speeds are the average of sFCOT and sESAT, ISO/IEC 29183.

Copy speed may vary depending on document complexity, copy mode, page coverage, type of paper used etc. and does not take into account warming up time.

<sup>[7]</sup> Full HD Movie Print is available for MOV and MP4 movie files created by select Canon digital cameras and camcorders. Requires installation of software bundled with Canon video or digital camera, from which the movie was captured. MOV files require: ZoomBrowser EX / ImageBrowser (version 6.5 or later), MP4 files require: ImageBrowser EX (version 1.0 or later).

<sup>[8]</sup> Easy-WebPrint EX requires Internet Explorer 8 or later

<sup>[9]</sup> When printing ISO/JIS-SCID N2 pattern on 10x15cm Photo Paper Plus Glossy II using default settings.

<sup>[10]</sup> When copying ISO/JIS-SCID N2 (printed by inkjet printer) on A4 size plain paper using default settings.

## Standard disclaimers

- All specifications subject to change without notice.
- Print speed may vary depending on system configuration, interface, software, document complexity, print mode, page coverage, type of paper used etc.
- Ink yield may vary depending on texts/photos printed, applications software used, print mode and type of paper used. For yield information see [www.canon-europe.com/ink/yield](http://www.canon-europe.com/ink/yield)
- Scan speed may vary depending on system configuration, interface, software, scan mode settings and document size etc.
- All brand and product names are trademarks of their respective companies.
- Microsoft, Windows and the Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries.



## SIMPLE AFFORDABLE FAMILY PRINTING WITH SMART CONNECTIVITY

# PIXMA TS5150

Fun and affordable, this small, stylish family printer takes all the hassle out of creating beautiful borderless images and documents at home with smart wireless connectivity to your devices and the cloud.

Sales Start Date: Sep 2017



### PRODUCT DETAILS:

Product Name	Mercury Code	EAN Code	Recommended Retail Price
PIXMA TS5150 BK EUR	2228C008AA	4549292090765	£89.99/ € 99.99

### CONSUMABLES:

Product Name	Mercury Code	EAN Code
<b>Standard size</b>		
PG-540	5225B005AA	8714574572536
CL-541	5227B005AA	8714574572581
<b>XL size</b>		
PG-540XL	5222B005AA	8714574572550
CL-541XL	5226B005AA	8714574572604

### MEASUREMENT / LOGISTIC INFORMATION:

Product Name	Mercury Code	Pack description	Quantity per pack	Length (mm)	Width (mm)	Height (mm)	Gross Weight (kg)	Net Weight (kg)
PIXMA TS5150 BK EUR	2228C008AA	Individual	1	501.3	222.1	465.4	8.4	6.4
		Pallet (Upper)	20	1,118.5	1,010.6	935.3	169.4	168
		Pallet (Bottom)	30	1,118.5	1,010.6	1,400.7	253.4	252

### What's in the box?

- All-In-One printer - PIXMA TS5150
- Setup Ink Tanks
- Power cord
- Setup CD-ROM
- Manuals