

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008701040](#)
Status: **Active**
Overview: Mini-SPOX Wire-to-Board Connector System
Description: 2.50mm Pitch Mini-SPOX Crimp Terminal, 22-28 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-5264-001-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	5263
Application	Signal
Crimp Quality Equipment	Yes
Overview	<u>Mini-SPOX Wire-to-Board Connector System</u>
Packaging Alternative	08-70-1039 (Reel)
Product Name	Mini-SPOX
UPC	800753534919

Physical


Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	43.200/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.90mm max.
Wire Size AWG	22, 24, 26, 28
Wire Size mm ²	N/A

Material Info

Engineering Number	5263PBTL
--------------------	----------

Reference - Drawing Numbers

Product Specification	PS-5264-001-001
Sales Drawing	SD-5263-003



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[5263 Series](#)

Use With

[5264 Mini-SPOX Crimp Housing](#)