

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0889416100](#)
Status: **Active**
Overview: [Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Pico-SPOX™ Female-to-Pico-SPOX™ Female, 300mm, 24 AWG
Replacement Part Number: <http://www.molex.com/molex/products/listview.jsp?channel=Products&sType=p&query=079758100779758-1007>

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	88900
Assembly Configuration	Pre-crimped Lead Only
Comments	Replacement Part# 79758-1007
Connector to Connector	Pico-SPOX™ Crimp Terminals
Overview	Pre-Crimped Leads
Product Name	Pico-SPOX™
Replacement Part Number	79758-1007
UPC	884982028128

Physical

Cable Length	0.30m
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.987/g
Packaging Type	Bag
Pitch - Mating Interface	1.50mm
Plating min - Mating	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Waterproof / Dustproof	No
Wire Size AWG	24
Wire/Cable Type	UL 1007

Electrical

Shielded No

Material Info

Reference - Drawing Numbers

Sales Drawing SD-88941-6100



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[88900 Series](#)

Mates With

[87421-0000 Crimp Terminals](#)

Use With

Pico-SPOX™ Housings [87439](#)