

# Prestigio ROADRUNNER DIAMOND

PCDVRR590W


## PURE QUALITY FOR YOUR SAFETY ON THE ROAD

RoadRunner Diamond is a new DVR from Prestigio which will provide you with the ultimate technology to ensure your safety on the road, whilst simultaneously being an exquisite addition to the design of your car. A beautiful appearance and metal body make the new DVR an appealing, reliable and durable device. The latest Ambarella A12 processor records video as Super HD and HD at 60 frames per second. High-quality night shooting will ensure you do not have to worry about accidents on the road in tricky light conditions. A 6 layer mirror lens, SONY matrix and a wide viewing angle of 150 degrees will capture every single detail. You will love the new expanded function: now you can update the firmware via Wi-Fi!



**SUPER HD**

1296P  
High Definition



Ambarella  
A12



Viewing  
Angle



Wi-Fi



Overheating  
Protection



Motion  
Detection

- **AMBARELLA A12:** The video quality is excellent — Ambarella A12 chipset ensures Super HD resolution and HD at 60 frames per second.
- **WIDE VIEWING ANGLE:** 150° wide viewing angle provides an extensive road overview.
- **BUILT-IN WI-FI:** Pair your Prestigio RoadRunner with your smartphone via Wi-Fi and increase its possibilities: view and download images and video, update firmware or even stream video.
- **SONY IMAGE SENSOR:** The Sony Sensor provides optimal image quality.
- **OVERHEATING PROTECTION SYSTEM:** It is expected that the battery will remain under 50° and overheating won't damage the device.
- **METAL HOUSING:** solid metal housing prevent device from scratches and damages.

<b>Display Size</b>	2.0"   960x240 px
<b>Processor</b>	Ambarella A12
<b>Resolution</b>	Video: 2304x1296 30fps, 1280x720 60fps
<b>Image Sensor</b>	2 MP CMOS   Sony IMX323
<b>Lens</b>	6-layer glass lens, Viewing Angle: 150°
<b>Format</b>	Video: AVI(MJPEG Codec), Photo: JPG
<b>Memory</b>	2 GB, up to 128 GB (SDHC, MicroSD)
<b>Other features</b>	Motion Detection, G-sensor, Cyclic recording, Automatic Night Vision, WiFi, HDR, FCMD, LLW, OVP, NTC.

<b>Connectivity</b>	Micro USB
<b>Built-in</b>	Microphone, Speaker
<b>Power</b>	Built in Re-chargeable battery (320 mAh) or from Car Power Adaptor
<b>Operation Temperature</b>	0 °~ 45 °C
<b>Dimensions</b>	66x50x18 mm
<b>Weight</b>	74 g
<b>In the box</b>	Suction mount, Crowbar for cable installation, Car Charger (3.6 meter) with 2 USB Ports