

AB-AV-1215 12MM IP40 STAINLESS STEEL LATCHING PUSH BUTTON SWITCH


SWITCHES

Specifications

Terminal type	Pin terminal (2.8x0.5mm)
Button	Flat high round
Switching	1NO Latching
Panel cut out	12mm
Switch rating	1A/36VDC
Contact resistance	$\leq 50\text{m}\Omega$
Insulation resistance	$\geq 1000\text{M}\Omega$
Dielectric strength	1500V RMS 50Hz
Operating temperature	-25°C~+55°C
Mechanical life	200,000 cycles
Electrical life	50,000 cycles
Panel thickness	1~10mm
Torque	0.6Nm max
Operating force	3.5N approx
Operation travel	2.5mm approx
IP degree	IP40
Material: Contact	Silver alloy
Button/Body	Stainless Steel
Base	PA66

ROHS Compliant

AB-AV-1215



Top view

Terminal Arrangement

Dimensions Unit: mm



ALAN BUTCHER COMPONENTS LTD

Alan Butcher Components Ltd
Unit 1 Beechwood Clump Farm Industrial Estate Tin Pot Lane Blandford Dorset DT11 7TD
Telephone 01258 456360 Facsimile 01258 459194 Email sales@abcomponents.co.uk
www.abcomponents.co.uk