

■ SPECIFICATIONS

ANTENNA	
PARAMETER	VALUE
Frequency Range	902 ~ 928 MHz
Output VSWR, max	1.5
Impedance	50 Ω
Gain	3.0 dBi
Wavelength	1/2 wave
Power, max	50 W
Polarization	Vertical
Connector Type	RPSMA Male
Length	205 mm
Weight, max	27 g

■ MECHANICAL SPECIFICATIONS



July 2017