

NEBO[®] SLYDE[®] KING



With all of the features that you would expect from a SLYDE[®]...and more! The 500 lumen SLYDE[®] KING is equipped with programmable memory settings for each light mode, a new C-O-B red light function, a 4x adjustable zoom and best of all...it's **rechargeable!**



4 LIGHT MODES

- Flashlight (500 lumens) - 2.5 hours / 160 meters
- C-O-B work light (500 lumens) - 3.5 hours / 37 meters
- Red light (40 lumens) - 5.5 hours / 9 meters
- Red flash - 24 hours / 9 meters

DESIGN

- Fully rechargeable
- Tactical edge
- OC™ Technology
- Convex lens
- 4x adjustable zoom
- Fully dimmable
- Memory Power Setting
- Anodized aircraft-grade aluminum; water and impact-resistant
- Powerful magnetic base
- Battery charging indicator

OPERATION

- Side-positioned, ON/OFF button; hold to dim
- C-O-B Work Light automatically turns ON when opened and OFF when closed

BATTERIES

- Powered by 1 Li-ion rechargeable battery included (3-4 hour recharge time)

ACCESSORIES

- Micro USB to USB cable included

SPECS

- 0.8 lbs.
- Length: Compacted: 6.875" / Extended: 9"
- Diameter: (Head) 1.75" / (Barrel) 1.25"

U.S. PATENT

- D786,466 S



OC Technology™ creates a perfectly dispersed beam of intense, pristine light that is as bright on the edge as it is in the center when used in flood mode.

CALIFORNIA REQUIRED WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov/product



Display Dimensions

(H) 11.5" x (W) 5.5" x (D) 7.875"

Gift Box Dimensions

(H) 6.79" x (W) 1.85" x (D) 1.82"

UPC CODE	ITEM	DESCRIPTION	CASE PACK
645397932635	6726	SLYDE [®] KING with Display	12 PIECES