



PRODUCT #: 880431

LEDLENSER EX7R

This Class 1, Div 1 flashlight makes work easier – not just because it weighs a mere 228 g (incl. batteries). The biggest reason is the Magnetic Switch. This on/off switch can easily be controlled with work gloves. And it's the first rechargeable flashlight for Class 1, Div 1 with patented Advanced Focus System. The included charging cradle makes charging the lithium-ion battery easy. But with a maximum battery life of 45 hours it will rarely need to be recharged.

KEY FEATURES:




- Rechargeable via charging cradle
- Magnetic Switch for easy operation with gloves and protective equipment
- Focusable

APPROVALS:

- Class 1, Division 1, Groups A,B,C,D;
- Class II, Division 1, Groups E,F,G; Class III, Temperature Code: T4
- ATEX: II 2G Ex ib IIC T4 Gb, II 2D Ex ib op is IIIC T135°C Db



WEIGHT: 8.04 oz. | 228 g
BATTERY: Rechargeable li-ion 3.7v

FL1 STANDARD	MAX	MIN
	220 LUMENS	50 LUMENS
	140m	65m
	10h	45h



Industry-leading Warranty

All Ledlenser products come backed by our industry-leading seven-year warranty. For more information about our warranty, please visit ledlenserusa.com.

ADDRESS:
 Ledlenser USA
 PO Box 20446
 Portland, OR 97294

PHONE:
 Local: (503) 408-5301
 Toll Free: (800) 650-1245

WEB:
www.ledlenserusa.com