



SECTION 1: Identification of the substance/mixture and of the company/undertaking

- 1.1 Product identifier** O'Keeffe's Healthy Feet Cream Jar
- 1.2 Relevant identified uses of the substance/mixture and uses advised against**
Foot Cream – skincare product
- 1.3 Details of the Supplier of the Safety Data Sheet**
Gorilla Glue Europe Ltd.
Chorley Business & Technology Centre
East Terrace, Euxton Lane,
Chorley, Lancashire
PR7 6TE
eusales@gorillaglu.com
- 1.4 Emergency telephone number**
+44 0843 507 1200

SECTION 2: Hazards identification

- 2.1 Classification of the substance or mixture**
This product is classified as not hazardous in accordance with Regulation (EC) No 1272/2008 (CLP).
- 2.2 Label elements**
- | Health Hazards | GHS Labeling |
|---------------------------|----------------------------|
| None Classified. | Hazardous Symbols: None |
| Physical Hazards | Signal Word: None |
| None Classified | Hazardous Statements: None |
| Hazard Category | Precautionary Statements |
| None Classified. | Prevention: None |
| Routes of Exposure | Response: None |
| None Classified. | Storage: None |
| | Disposal: None |
- 2.3 Other hazards**
None if used properly.

SECTION 3: Composition / information on ingredients

Hazardous components

Chemical Name	Concentration %
Sodium Hydroxide	*

*concentration is proprietary

SECTION 4: First aid measures

4.1 Description of first aid measures

Eyes

Immediately flood the eye with plenty of water for at least 15 minutes, holding the eye open. Obtain medical attention if soreness or redness persists.

Skin

None

Ingestion

Rinse mouth out and drink plenty of water.

Inhalation

Under normal conditions of use, no expected risks are posed by inhalation. If irritation occurs, seek fresh air.

Advice to Physicians

Treat symptomatically.

4.2 Most important symptoms and effects, both acute and delayed

Skin: Mild stinging sensation may occur.

4.3 Indication of any immediate medical attention and special treatment needed

See Section 4.1 Description of first aid measures.

SECTION 5: Firefighting measures

5.1 Extinguishing Media

Suitable extinguishing media:

Not Flammable - Use any extinguishing media that is suitable for the surrounding fire.

Extinguishing media which must not be used for safety reasons:

None – Use any extinguishing media that is suitable for the surrounding fire.

5.2 Special hazards arising from the substance or mixture

None.

5.3 Advice for firefighters

Please wear the appropriate protective clothing and/or breathing apparatus that is suitable for the surrounding fire.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment, and emergency procedures

No special measures are required.

6.2 Environmental precautions

No special measures are required.

6.3 Methods and materials for containment and cleaning up

Scoop up and transfer material into a suitable container for recovery or disposal. Wash spilled area thoroughly with soap and water.

6.4 Reference to other sections

Please see Section 8.

SECTION 7: Handling and storage

7.1 Precaution for safe handling

None necessary.

7.2 Conditions for safe storage, including any incompatibilities

Store at room temperature.

7.3 Specific end use(s)

Hand Cream

SECTION 8: Exposure controls / personal protection

8.1 Control parameters

Sodium Hydroxide		
Austria	MAK	2 mg/m ³
Austria	KZW	4 mg/m ³
Belgium	TWA	2 mg/m ³
Denmark	CL	2 mg/m ³
Finland	CL	2 mg/m ³
France	VME	2 mg/m ³
Hungary	TWA	2 mg/m ³
Iceland	STEL	2 mg/m ³
Netherlands	MAC-TGG	2 mg/m ³
Norway	TWA	2 mg/m ³
Poland	MAC (TWA)	0,5 mg/m ³
Poland	MAC (STEL)	1 mg/m ³
Sweden	TWA	1 mg/m ³
Sweden	CL	2 mg/m ³ (inhalable dust)
Switzerland	CL	2 mg/m ³ (inhal)
Turkey	TWA	2 mg/m ³
United Kingdom	STEL	2 mg/m ³

8.2 Exposure controls

Engineering control

No specific measures necessary.

Personal Protective Measures

Respiratory/Skin/Eye/Face/Body Protection

Not required when used under normal conditions.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical State	Solid: cream	pH	6.0 – 7.8
Color	White	Density (g/l, g/yd²)	Not applicable
Odor	Mild Stearic Acid odor	Specific Gravity	1.03 – 1.06 g/ml
Odor Threshold	No data available	Melting Point (°C/F)	Not applicable
Boiling Range/Point (°C/F)	> 100°C	Vapor Pressure	Not applicable
Flash Point (PMCC) (°C/F)	None	Solubility in Water	Not Miscible
Evaporation Rate (BuAc=1)	Not applicable	Viscosity	Not applicable
Vapor Density (Air = 1)	Not applicable	Auto-Ignition Temperature	Not applicable
VOC (g/l)	Not applicable	Decomposition Temperature	Not applicable
VOC (%)	Not applicable	Upper Explosive Limit	Not applicable
Partition Coefficient (n-octanol/water)	Not applicable	Lower Explosive Limit	Not applicable
Flammability (solid / gas)	Not applicable		

9.2 Other information

No data available.

SECTION 10: Stability and reactivity

10.1 Reactivity

Data is not available.

10.2 Chemical stability

Stable under normal conditions.

10.3 Possibility of hazardous reactions

None.

10.4 Conditions to avoid

None.

10.5 Incompatible materials

None.

10.6 Hazardous decomposition products

None.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

No relevant studies identified.

Specific target organ systemic toxicity (STOT single and repeat)

No relevant studies identified.

Serious eye damage / eye irritation

No relevant studies identified.

Skin corrosion / irritation

Studies identified no skin irritation.

Respiratory sensitization

No data is available to indicate this product may be a respiratory sensitizer.



Skin sensitization

Studies identified no skin sensitization.

Carcinogenicity

No relevant studies identified.

Germ cell mutagenicity

No relevant studies identified.

Aspiration hazard

No relevant studies identified.

SECTION 12: Ecological information

12.1 Toxicity / 12.2 Persistence and degradability / 12.3 Bioaccumulative potential / 12.4 Mobility in soil / 12.5 Results of PBT and vPvB assessment / 12.6 Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Dispose of in accordance with all applicable local, state, federal, and national regulations.

SECTION 14: Transport information

14.1 UN number / 14.2 UN proper shipping name / 14.3 Transport hazard class(es) / 14.4 Packaging group

Not dangerous goods.

14.5 Environmental hazards / 14.6 Special precautions for user 14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations / legislation specific for the substance or mixture

No information is available.

15.2 Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The information presented in this Safety Data Sheet was prepared by qualified personnel and to the best of our knowledge is true and accurate. The information and recommendations are furnished for this product with the understanding that the purchaser will independently determine the suitability of the product for this purpose. This data does not constitute a warranty, expressed or implied, statutory or otherwise, nor is it representation for which the O'Keeffe's Company assumes legal responsibility. The data is submitted for the user's information and consideration only. Any use or disposal of this product must be determined by the user to be in with applicable national, federal, state, provincial and local laws and regulations.