


G12T-75



Featured in the world's top selling 4x12 cabinet, the G12T-75 guitar speaker is a high powered rock player's dream. Built to meet the demands of high gain amplifiers, the G12T-75 combines a huge, tightly controlled low-end and aggressive mid-range with a softened top-end that adds a welcome sweetness to overdrive, distortion and aggressive upper harmonics. These are the characteristics that make the G12T-75 the weapon of choice for Yngwie Malmsteen.

8 Frequency Response



General Specifications

Nominal diameter	12", 305mm
Power rating	75Wrms
Nominal impedance	Available 8 or 16
Sensitivity	97dB
Chassis type	Pressed steel
Voice coil diameter	1.75", 44.5mm
Voice coil material	Round copper
Magnet type	Ceramic
Magnet weight	35oz, 0.99kg
Frequency range	80-5000Hz
Resonance frequency, Fs	85Hz
DC resistance, Re	Available 6.77 or 12.9

Mounting Information

Cut-out diameter	11.1", 283mm
Diameter	12.2", 309mm
Magnet structure diameter	5.7", 145mm
Mounting slot dimensions	0.31", 7.9mm Ø
Mounting slot PCD	11.7", 297mm
Number of mounting slots	4
Overall depth	5.0", 127mm
Unit weight	7.7lb, 3.5kg