



PRODUCT #: 880433

LEDLENSER iL4

As small and handy as a pen but as rugged and most importantly as safe as other lamps in the iL series: The Ledlenser iL4. Designed specifically for environments where explosive atmospheres such as flammable gases, vapors or dust clouds can occur for a short period. And yet it's the cheapest lamp in the iL series. So not even costs will explode.

KEY FEATURES:




- Extremely lightweight (65 g incl. batteries)
- Extremely small and handy (L 14.0 cm)
- Battery operated, uses 2x alkaline AAA

APPROVALS:

- Class 1, Division 2, Groups A,B,C,D;
- Class II, Division 1, Groups E,F,G; Class III, Temperature Code: T4
- ATEX: II 3G Ex ic IIC T4 Gc, II 3D Ex ic IIIC T135°C Dc



WEIGHT: 2.29 oz. | 65 g
BATTERY: 2x alkaline AAA

FL1 STANDARD	MAX
	80 LUMENS
	50m
	4h



Industry-leading Warranty

All Ledlenser products come backed by our industry-leading seven-year warranty. For more information about our warranty, please visit ledlenserusa.com.

ADDRESS:

Ledlenser USA
 PO Box 20446
 Portland, OR 97294

PHONE:

Local: (503) 408-5301
 Toll Free: (800) 650-1245

WEB:

www.ledlenserusa.com