

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0190350004**  
**Status:** **Active**  
**Overview:** Snap Plugs and Receptacles  
**Description:** Avikrimp Snap Plug, for 18-22 AWG Wire, Mylar Tape, 22.55mm Length

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E152602

**General**

Product Family Quick Disconnects  
 Series 19035  
 Comments Molded Nylon Insulation  
 Crimp Quality Equipment Yes  
 Insulated Partial  
 Overview Snap Plugs and Receptacles  
 Product Name Avikrimp  
 Type Snap Plug  
 UPC 800753047860

**Physical**

Barrel Type Closed  
 Color - Resin Red  
 Flammability 94V-2  
 Gender Male  
 Glow-Wire Capable No  
 Insulation Nylon (PA)  
 Lock to Mating Part None  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Material - Resin Nylon  
 Net Weight 2.987/g  
 Orientation Straight  
 Packaging Type Adhesive Tape on Reel  
 Tab Thickness N/A  
 Tab Width N/A  
 Wire Insulation Diameter 3.60mm max.  
 Wire Size AWG 18, 20, 22

**Electrical**


Voltage - Maximum N/A

**Material Info**

Engineering Number A-569T

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-015-001  
 Sales Drawing SD-19035-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/61/2018 (27 June  
 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

19035 Series