

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190840004](#)
Status: **Active**
Overview: [Solderless Terminals](#)
Description: Open Barrel Star Ring , Tin-Plated Brass, for 14-18 AWG Wire Range, Stud Size 6 (M3.5)

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-011-001 \(PDF\)](#)
[Product Specification PS-19902-006-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series [19084](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [Solderless Terminals](#)
Product Name N/A
Type Ring
UPC 800755080193

Physical

Barrel Type Open
Insulation None
Material - Plating Mating Tin
Net Weight 0.827/g
Packaging Type Reel
Plating min - Mating 2.540µm
Plating min - Termination 2.540µm
Stud Size 6 (M3.5)
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter N/A
Wire Size AWG 14, 16, 18
Wire Size mm² 0.80-2.00

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number SRZ-4129-06

Reference - Drawing Numbers

Product Specification PS-19902-006-001, PS-19902-011-001
Sales Drawing SD-19084-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19084 Series](#)