

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0532580829
Status: Active
Description: 3.50mm Pitch Header, Vertical, 8 Circuits, Brass (CuZn) Contact

Documents:

- 3D Model
- Drawing (PDF)
- Product Specification PS-51067-019-001 (PDF)
- Packaging Specification SPK-53258-001-001 (PDF)
- RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family PCB Headers
Series 53258
Application Power, Wire-to-Board
Product Name N/A
UPC 822348254071

Physical

Breakaway No
Circuits (Loaded) 8
Circuits (maximum) 8
Durability (mating cycles max) 30
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Capable No
Guide to Mating Part Yes
Keying to Mating Part None
Lock to Mating Part Yes
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 1902.500/mg
Number of Rows 1
Orientation Vertical
PC Tail Length 3.50mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 3.50mm
Plating min - Mating 1.016µm
Plating min - Termination 1.016µm
Polarized to PCB No
Shrouded Fully
Stackable No
Temperature Range - Operating -40° to +105°C
Termination Interface: Style Through Hole


Electrical

Current - Maximum per Contact 5.5A
Voltage - Maximum 250V

Material Info

Reference - Drawing Numbers

Packaging Specification SPK-53258-001-001



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

53258 Series

Mates With

51067 Wire-to-Wire and Wire-to-Board
Housing

This document was generated on 10/11/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION