

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008550101](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: KK 254 Crimp Terminal, 22-30 AWG, Reel, Selective Gold (Au), Nickel (Ni) Under Plating

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-002-001 \(PDF\)](#)
[Product Specification PS-10-07-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification TS-10-07-001 \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [2759](#)
 Application Signal, Wire-to-Board
 Crimp Quality Equipment Yes
 Overview [KK® Interconnect System - Molex](#)
 Packaging Alternative [08-55-0102 \(Loose\)](#)
 Product Name KK 254
 UPC 800753749900

Physical

Gender Female
 Material - Metal Brass
 Material - Plating Mating Gold
 Material - Plating Termination Nickel
 Net Weight 0.064/g
 Packaging Type Reel
 Plating min - Mating 0.381µm
 Plating min - Termination 0.762µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.57mm max.
 Wire Size AWG 22, 24, 26, 28, 30
 Wire Size mm² N/A

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number 2759-(555)B

Reference - Drawing Numbers

Packaging Specification PK-2759-002-001
 Product Specification PS-10-07-001, TS-10-07-001
 Sales Drawing SD-2759



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[2759 Series](#)

Use With

[2695](#) , [5051](#)