

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008550124](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: KK High Pressure Crimp Terminal 7879, 22-30 AWG, Reel Selective Gold (Au)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-002-001 \(PDF\)](#)
[Product Specification PS-7879-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [7879](#)
 Application Signal, Wire-to-Board
 Crimp Quality Equipment Yes
 Overview [KK® Interconnect System - Molex](#)
 Packaging Alternative [08-55-0129 \(Loose\)](#)
 Product Name KK High Pressure
 UPC 800753614185

Physical

Gender Female
 Material - Metal Brass
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Net Weight 0.117/g
 Packaging Type Reel
 Plating min - Mating 0.381µm
 Plating min - Termination 2.540µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.57mm max.
 Wire Size AWG 22, 24, 26, 28, 30
 Wire Size mm² N/A

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number 7879-1(P208)

Reference - Drawing Numbers

Packaging Specification PK-2759-002-001
 Product Specification PS-7879-001
 Sales Drawing SD-7879



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[7879 Series](#)