

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982670211](#)
Status: **Active**
Overview: Premo-Flex Cable Jumpers
Description: 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 6 Circuits, 0.152m Cable Length, Tin(Sn) Plating

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-98267-001-001 \(PDF\)](#) [Product Literature \(PDF\)](#)

General

Product Family Cable
 Series [98267](#)
 Comments Contacts on the same side, Type A
 Crimp Quality Equipment Yes
 Overview [Premo-Flex Cable Jumpers](#)
 Product Literature Order No 987650-6631
 Product Name Premo-Flex FFC Jumper
 UPC 756054770214

Physical

Cable Length 0.152m
 Circuits (Loaded) 6
 Circuits (maximum) 6
 Net Weight 0.687/g
 Packaging Type Bag
 Pitch - Termination Interface 1.00mm
 Temperature Range - Operating -40° to +105°C
 Wire Size AWG N/A
 Wire/Cable Type Flat Flex Cable

Electrical

Current - Maximum per Contact 1.2A
 Voltage - Maximum 60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification PK-98267-001-001
 Sales Drawing SD-98267-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[98267 Series](#)

Use With

[52207](#) , [52271](#) , [52852](#) , [52793](#) , [52808](#)
 , [52610](#) , [52807](#) , [52030](#) , [52806](#)

 Molex FFC – FPC connector. Be sure to
 match like plating.