



VERY WIDE SPREAD OF LIGHT

POWERFUL LEDs

3 BRIGHTNESS LEVELS

ESD SAFE WITH A MODERN & ERGONOMIC DESIGN

Luminos ESD

TABLE LAMP

This powerful LED lamp provides the ultimate in high light output with special conductive coatings and materials to guarantee ESD compliance. It has an exceptionally wide spread of light, that is dimmable. Ideal for work benches and illuminating detail large surfaces. The arm has a long reach of 112cm (44.1") and can be moved easily with one hand. The shade can be positioned effortlessly, exactly where it is needed.

5
great
reasons to
use Daylight
lamps



DESIGN
& FUNCTION



BRIGHTER



CLARITY



ERGONOMICS



MAGNIFICATION

+44 (0)20 8964 1200
www.daylightcompany.com




daylight
when light matters

D/E35611

Luminos ESD

- ★ Ergonomic and professional ESD safe lamp
- ★ Very wide shade 65cm (25½")
- ★ Suitable for use in EPA, (Electrostatic Protected Areas) To IEC 61340-5-1 and ANSI/ESD 20:20
- ★ 120 powerful daylight LEDs provide true colour matching
- ★ 3 brightness levels
- ★ Effortless free-motion head joint & arm - holds any position
- ★ Heavy duty arm with reinforced joints and covers



Product Information

Width	65cm (25.6")
Height	60cm (23.6")
Depth	75cm (29.5")
Weight	3.2kg (7.1lb)
Colour	Black
Reach	112cm (44.1")
Cable Length	2.4m (94.5")

Light Output

Light Source	LED
Lumens	1,566lm
Lux	3,800 Lux at 30cm (12")
Colour Temperature	6,000°K
Power Consumption	24W

Packaging Information

Width	90cm (35.4")
Height	40.5cm (15.9")
Depth	10.2cm (4")
Packed Weight per unit	4.5kg (10lbs)
Products per Master Carton	2

+44 (0)20 8964 1200
www.daylightcompany.com

