



45W

VT-645 45W LED PANEL LIGHT-60x60 WITH SAMSUNG CHIP
 COLORCODE:4000K 5 YRS WARRANTY

Lumens 3600	Beam Angle 110	Dimensions 595x595x14mm
-----------------------	--------------------------	-----------------------------------

Day White
 SKU:633



Technical Information

Watts:	45	LED Chip Type:	SMD
Lumens:	3600	IP Rating:	IP20
Shape:	Square	Dimmable:	No
Beam Angle:	110	Warranty (Years):	5
Unit Color:	White	PF:	>0.9
Body Type:	Aluminum+PMMA+PP	CRI:	>80
Long life:	30,000 Hours	Input Power:	AC:220-240V,50Hz

Features

- ✓ Flicker Free
- ✓ Highly Efficient LED Samsung Chip
- ✓ Higher Light Transmission Rate
- ✓ Quick connector making the installation easy - Plug & Play
- ✓ High quality power driver ensures reliable lifetime - Smart Driver Box
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Strong Aluminium body and efficient heat dissipation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Easy to install & Low Maintenance
- ✓ Complies with LM-80
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Listing Details

EAN Code

3800157634311

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES