



UnoLamps

CLAMP, TABLE & FLOOR LAMPS

These slim, flexible lamps have a modern design and sleek finish. They have 28 high performance, energy efficient daylight LEDs providing high light output over a large area.



+44 (0)20 8964 1200
www.daylightcompany.com





UNOLAMPS

D/EN1410: UnoLamp with clamp

D/EN1420: UnoLamp Table

D/EN1430: UnoLamp Floor

- ★ Flexible arm directs light exactly where you need it
- ★ 28 high quality bright LEDs provide accurate colour matching
- ★ Touch switch dimmer with 4 brightness levels
- ★ Lamp brightness: 1,145 Lux at 30cm (12")



	UnoLamp with Clamp	UnoLamp Table	UnoLamp Floor
Product Dimensions (HxWxD)	28.5 x 39 x 6.5cm (11.2" x 15.4" x 2.6")	38.5 x 36 x 12cm (15.2" x 14.2" x 4.7")	132 x 46 x 21cm (52" x 18.1" x 8.3")
Product Weight	0.4kg (0.9lb)	0.5kg (1lb)	3.2kg (7.1lb)
Maximum Reach	20cm (7.9")	36.5cm (14.4")	48.5cm (19.1")
Cable Length	1.7m (66.9")	1.5m (59.1")	1.8m (68.9")
Light Source	LED	LED	LED
Lumens	400 lm	400 lm	400 lm
Energy Consumption	6W	6W	6W
Light Colour Temperature	6,000°K	6,000°K	6,000°K
Box dimensions (HxWxD)	35 x 12.5 x 7cm (13.8" x 4.9" x 2.8")	35 x 17.5 x 12.5cm (13.8" x 6.9" x 4.9")	36.5 x 24.5 x 12cm (14.4" x 9.6" x 4.7")
Total Weight	0.43kg (1lb)	0.7kg (1.5lb)	3.5kg (7.6lb)
Products per Master carton	12	8	3

+44 (0)20 8964 1200
www.daylightcompany.com

