



# DuoLamps

## CLAMP, TABLE & FLOOR LAMPS

These slim, flexible lamps have a modern design and sleek finish. They have 28 high performance, energy efficient daylight LEDs providing high light output over a large area.



+44 (0)20 8964 1200  
[www.daylightcompany.com](http://www.daylightcompany.com)



# DUOLAMPS

D/EN1510: DuoLamp with clamp

D/EN1520: DuoLamp Table

D/EN1530: DuoLamp Floor

- ★ Double head increasing your illuminated work surface
- ★ Flexible arm directs light exactly where you need it
- ★ 56 high quality bright LEDs provide accurate colour matching
- ★ Touch switch dimmer with 4 brightness levels
- ★ Lamp brightness: 2,090 Lux at 30cm



	DuoLamp with Clamp	DuoLamp Table	DuoLamp Floor
Product Dimensions (HxWxD)	28,5 x 46 x 6,5cm	38,5 x 43 x 12cm	132 x 53 x 21cm
Product Weight	0,5kg	0,8kg	3,5kg
Maximum Reach	28,5cm	45cm	57cm
Cable Length	1,7m	1,5m	1,8m
Light Source	LED	LED	LED
Lumens	700 lm	700 lm	700 lm
Energy Consumption	10W	10W	10W
Light Colour Temperature	6000°K	6000°K	6000°K
Box dimensions (HxWxD)	43 x 12,5 x 7cm	40 x 20,5 x 12,5cm	42,5 x 26,5 x 12cm
Total Weight	0,6kg	1kg	3,6kg
Products per Master carton	12	8	3

+44 (0)20 8964 1200  
[www.daylightcompany.com](http://www.daylightcompany.com)

