

Outdoor Curve Wall Light 7.5W 3000K 360lm IP54

Partcode: ILDEA008 / Page: 1



Discover Integral's new outdoor range. Light up the exterior of your home with these compact, stylish and contemporary LED luminaires. Weatherproof and hard-wearing, this range is designed to last against the elements while bringing a designer look to your surroundings.

Sleek and sophisticated, the Curve wall light is the ideal accessory to light up your outdoor space.

[Watch Video](#)

Product Details

Partcode: ILDEA008

Check Code: 306447

Range Name: Outdoor

Product Type: Outdoor

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Optic: Opal Polycarbonate diffuser

Material: Die cast aluminium body with powder coated finish

Physical Data

Length: 270mm
Width: 82mm
Depth: 112mm
Weight (Unpackaged Single Unit): 675g
Luminaire Fixing: Wall Mounted


Electrical Data

Voltage Range: 220-240V
Power Consumption: 7.5 Watts
Driver included: Yes
Electric Current: AC
Ampage: 350.00mA
Frequency Range: 50/60 Hz
Power Factor: ≥ 0.80
Dimming: Non-dimmable
LVD Certified: Yes
EN: EN-60598

Light Data

Lumens: 360lm
Lumens per Watt: 48.0lm/W
Correlated Colour Temperature (CCT): 3,000k
Colour Temperature: Warm White
Colour Rendering Index (CRI): ≥ 80
LED Type: Surface mounted device (SMD)
Instant on - Less than 1 second: Yes
Lifetime: 25,000 hrs
Switching Cycles: $>12,500$ X

Environmental




Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP54

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788232605

Packaged Weight (Unit of 1): 780g

Length (unit of 1): 285mm

Width (unit of 1): 95mm

Depth (unit of 1): 120mm

Outer packaging info available on website

Product data last updated on: Thursday, October 25, 2018 - 16:17