

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0887418300**
Status: **Active**
Overview: MicroCross DVI Connectors and Cable Assemblies
Description: MicroCross DVI Digital Visual Interface, Shielded I/O Cable Assembly: DVI-Analog-to-VGA, Black, 2.0m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-88741-004 \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	88744
Assembly Configuration	Dual Ended Connectors
Connector to Connector	DVI-Analog-to-VGA
Overview	<u>MicroCross DVI Connectors and Cable Assemblies</u>
Product Name	MicroCross DVI
UPC	800754018616

Physical

Cable Length	2.0m
Circuits (Loaded)	29
Color - Resin	Black, Natural
Gender	Plug/Plug
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Low Density Polyethylene, Polyester
Net Weight	227.089/g
Packaging Type	Bag
Pitch - Mating Interface	1.90mm, 2.54mm
Plating min - Mating	0.051µm, 0.254µm
Plating min - Termination	3.810µm
Single Ended	No
Termination Interface: Style	Solder or Weld
Wire Insulation Diameter	N/A
Wire Size AWG	N/A
Wire/Cable Type	N/A


Electrical

Current - Maximum per Contact	3.0A
Shielded	Yes

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-88741-004
Sales Drawing	SD-88741-004



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(a)-I

REACH SVHC

Contained Per - ED/01/2018 (15 January 2018) 2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

88744 Series

Mates With

74320 MicroCross DVI-I Digital/Analog Visual Interface, PCB Receptacle