



Einhell Germany AG

Einhell

CLASSIC

GC-EL 2500 E

Electric Leaf Vacuum

Item No.: 3433300

Ident No.: 11015

Bar Code: 4006825610352

The GC-EL 2500 E electric blower vac is a powerful tool and reliable helper for gardeners who want to clean up their grounds and gardens. The change-over between the blow and vacuum function without tools allows the blower vac to be quickly adjusted to the job in hand. The electronic speed control enables the suction and blowing power to be exactly dosed. Two guide wheels ensure comfortable and back-friendly operation on paths, lawns and difficult terrain. With the adjustable carrying strap this electric blower vac can be comfortably carried over difficult terrain for back-friendly operation with minimum effort.

Features

- On/Off switch
- Selector switch for vacuum/blower
- Large 2-piece suction tube
- 2 guide rollers
- Electronic speed control
- Debris bag approx. 40 l
- Adjustable carrying strap

Technical Data

- Mains supply	230-240 V 50 Hz
- Power	2500 W
- Idle speed	7000 - 13500 min ⁻¹
- Blow velocity	240 km/h
- Max. suction power	650 m ³ /h
- Shredding function	10:1
- Capacity of catch bag	40 L

Logistic Data

- Product weight	3.24 kg
- Gross weight single packaging	3.86 kg
- Dimensions single packaging	335 x 440 x 185 mm
- Pieces per export carton	1 Pieces
- Gross weight export carton	3.86 kg
- Dimensions export carton	445 x 190 x 340 mm
- Container quantity (20"/40"/40"HC)	1008 2177 2442

