

Canon CanoScan LiDE 300(2995C010)

Canon CanoScan LiDE 300 - Flatbed scanner - A4/Letter - 2400 dpi x 4800 dpi - USB 2.0



Compact and affordable, this lightweight scanner is perfect for those wanting straightforward scanning at the touch of a button.

Key Selling Points

- Compact, sleek and affordable scanner for home or office
- Pristine borderless prints
- Instant access
- Freedom of the cloud
- Maximize your money
- Get creative

Product Features

Compact, sleek and affordable scanner for home or office

With a sleek, compact and stylish design, this lightweight A4 flatbed scanner is fitted with 4 EZ operation buttons for easy use and hassle-free scanning. Perfect for high-resolution scanning at home or in the office.

Pristine borderless prints

Effortlessly print stunning borderless photos from 4x6 inch to A4, filled with fine detail and documents with sharp text for high-quality results.

Instant access

Enjoy straightforward printing, copying and scanning using your smartphone or tablet or directly access cloud storage via PIXMA Cloud Link - all thanks to the Canon PRINT app.

Freedom of the cloud

Print and scan documents to cloud services such as GoogleDrive, OneDrive and Dropbox. You can also attach and send scanned files directly via email - all without a PC.

Maximize your money

Cut waste and boost your cost savings by up to 50% compared to standard cartridges with optional XL ink cartridges and auto 2-sided printing.

Get creative

Unleash your inner artist with Creative Park and the Easy PhotoPrint Editor. Use the app to design cards, calendars and more using photos from your tablet, PC or cloud.

Main Specifications

Product Description	Canon CanoScan LiDE 300 - flatbed scanner - desktop - USB 2.0
Device Type	Flatbed scanner - desktop
Interface Type	USB 2.0
Scan Element Type	Contact Image Sensor (CIS)
Light Source	3-colour RGB LED
Additional Functions	Scan to cloud
Max Supported Document Size	216 x 297 mm
Input Type	Colour
Grayscale / Color Depth	16-bit (64K grey levels) / 48-bit colour
Grayscale / Color Depth (External)	8-bit (256 grey levels) / 48-bit colour
Optical Resolution	2400 dpi x 4800 dpi
Interpolated Resolution	19200 dpi
Max Document Size	216 mm x 297 mm

Supported Document Type	Plain paper,bulk objects (such as books,magazines and other bound materials)
System Requirements	Microsoft Windows 7,Microsoft Windows 7 SP1,Windows 8.1,Windows 10,Apple MacOS X 10.12 - 10.13,Apple MacOS X 10.11.6
Dimensions (WxDxH)	25 cm x 36.7 cm x 4.2 cm
Weight	1.7 kg

Extended Specification

General

Type	Flatbed scanner - desktop
Interface Type	USB 2.0
Additional Functions	Scan to cloud
Max Supported Document Size	216 x 297 mm

Scanner

Input Type	Colour
Grayscale Depth	16-bit (64K grey levels)
Grayscale Depth (External)	8-bit (256 grey levels)
Colour Depth	48-bit colour
Colour Depth (External)	48-bit colour
Optical Resolution	2400 dpi x 4800 dpi
Interpolated Resolution	19200 dpi
Scan Element Type	Contact Image Sensor (CIS)
Bulb / Light Source Type	3-colour RGB LED
Control Panel Buttons Functions	Copy,AutoScan,send to,PDF

Scanner Speed Details	10 sec/scan - colour - A4 - 300 dpi 5 sec/scan - colour - 4x6 - 300 dpi 9 sec/scan - preview 14.8 ms/line - colour - 2400 dpi 6.6 ms/line - colour - 1200 dpi 3.8 ms/line - colour - 600 dpi 2.2 ms/line - colour - 300 dpi 4.3 ms/line - greyscale - 2400 dpi 2.2 ms/line - greyscale - 1200 dpi 1.3 ms/line - greyscale - 600 dpi 2.2 ms/line - greyscale - 300 dpi
-----------------------	---

Scanner Features	Auto Document Fix,Auto Scan Mode,Auto Photo Fix,4 EZ Buttons,Advanced Z-lid Expansion Top
------------------	---

Media Handling

Max Document Size	216 mm x 297 mm
Supported Document Type	Plain paper,bulk objects (such as books,magazines and other bound materials)

Expansion / Connectivity

Interfaces	USB 2.0 - Mini-B
------------	------------------

Miscellaneous

Cables Included 1 x USB cable

Power

Power Consumption Operational (Standby) 4.5 Watt

Power Consumption Stand by 0.3 Watt

Software / System Requirements

Software Included Drivers & Utilities

OS Required Microsoft Windows 7,Microsoft Windows 7 SP1,Windows 8.1,Windows 10,Apple MacOS X 10.12 - 10.13,Apple MacOS X 10.11.6

Dimensions &Weight

Width 25 cm

Depth 36.7 cm

Height 4.2 cm

Weight 1.7 kg

Environmental Parameters

Min Operating Temperature 5 °C

Max Operating Temperature 35 °C

Humidity Range Operating 10 - 90% (non-condensing)

What's in the box

Canon CanoScan LiDE 300
USB cable
Drivers &Utilities

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet