



General ordering data

Order No.	1689990000
Part designation	ZDK 2.5V
Version	Modular terminal, 2.5 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
EAN	4008190875459
Qty.	50 pc(s).

Product notes

Note, technical data	2.5 mm ² flexible conductors with wire end ferrules are crimped with the Weidmüller PZ 6/5 crimping tool.
Product description	Z-series standard ranges provide solutions for conductor cross-sections from 0.05 to 35 mm ² .

PT OKIECEEx/ATEX rating data

EU-type examination certificate	KEMA97ATEX4677U
Download, German	KEMA97ATEX4677U_d.pdf
Download English	KEMA97ATEX4677U_e.pdf
ATEX voltage	440 V
ATEX current	20 A
ATEX conductor cross-section	2.5 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG-Baumusterprüfbescheinigung/IECEx-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	dark beige
Connection direction	top
End plate required	Yes
Explosion-tested version "Ex e"	Yes
Installation advice	TS 35

Additional technical data

Insulating material	Wemid
Levels cross-connected internally	Yes
No. of identical terminals	1
No. of levels	2
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 50 °C, + 120 °C
Product family	Z-series
Type of connection	Clamped
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	Double terminal

CSA rating data

Voltage (CSA)	300 V
CSA current	10 A
Min. cross-section (CSA)	AWG 26
Max. cross-section (CSA)	AWG 12

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	2.5 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.05 mm ²
Clamping range, max.	2.5 mm ²
Type of connection	Tension clamp connection
2nd type of connection	clamped
Connection direction	top
No. of connections	2
Stripping length	10 mm
Blade size	0.6 x 3.5 mm
Gauge to IEC 60947-1	A2
Solid, min.	0.5 mm ²
Solid, max.	2.5 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	2.5 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	2.5 mm ²
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	0.5 mm ²
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	2.5 mm ²
AWG conductor size, min.	AWG 26
AWG conductor size, max.	AWG 12
AWG conductor size, min.	0.13 mm ²
AWG conductor size, max.	3.31 mm ²

Dimensions

Width	5.1 mm
-------	--------

Dimensions

Height of lowest version	54 mm
Length	79.5 mm
TS 35 offset	39 mm

Rating data

Rated cross-section	2.5 mm ²
Rated voltage	500 V
Rated impulse voltage	6 kV
Rated current	20 A
Standards	IEC 60947-7-1
Current with max. conductor	24 A
Pollution severity	3

UL rating data

Voltage (UL)	300 V
Current (UL)	10 A
Min. cross-section (UL)	AWG 30
Max. cross-section (UL)	AWG 12

Approvals

Approvals institutes



Downloads

DXF	24215_ZDK2.5V_DXF.dxf
STEP	1689990000_24215_ZDK_2.5V_STP.stp

Classifications

ETIM 2.0	EC000897
ETIM 3.0	EC000897
eClass 4.1	27-14-11-18
eClass 5.0	27-14-11-18
eClass 5.1	27-14-11-18

Similar products

Order No.	Part designation	Version
1674300000	ZDK 2.5	Modular terminal, 2.5 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1678630000	ZDK 2.5 BL	Modular terminal, 2.5 mm ² , Tension clamp connection, Wemid, blue, TS 35

1689970000	ZDK 2.5DU-PE	Modular terminal, 2.5 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1689960000	ZDK 2.5N-DU	Modular terminal, 2.5 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1689980000	ZDK 2.5N-PE	Modular terminal, 2.5 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1694140000	ZDK 2.5 OR	Modular terminal, 2.5 mm ² , Tension clamp connection, Wemid, Orange, TS 35
1745880000	ZDK 2.5V BL	Modular terminal, 2.5 mm ² , Tension clamp connection, Wemid, blue, TS 35