

# KUBO3-BL

3" compact design full range cabinet loudspeaker, black




The compact KUBO3 design loudspeaker comes with a 3" full range driver unit and bass reflex port providing a fast and dynamic bass response. The exceptional symmetrical cube-shaped designed KUBO3 produces 40 watts dynamic power at 8 ohms. The K-Mount bracket combined with the carefully designed fixing K-bolts grant you a safe and comfortable loudspeaker hook-up.

The easy cable management and 140° vertical or horizontal mounting possibility allows you to install the KUBO3 everywhere on any type of wall or ceiling. The in & link connection with euroblock connectors, offers easy daisy chaining of multiple KUBO loudspeakers. The installer friendly end-caps, held in place by 14 integrated strong neodymium magnets, hide all connections and bracket hardware on both sides. The unseen original and timeless KUBO cabinet will blend audio in with any kind of interior, adding elegance to any architect designed environment.

## TECHNICAL SPECIFICATIONS

height in mm	125	width in mm	131
depth in mm	109	loudspeaker system	full range
woofer size in inch	3	woofer cone material	polypropylene
mounting system	U-bracket	colour	black / white
impedance (ohms)	8	low impedance dynamic power in watts	40
low impedance RMS power in watts	25	SPL 1W/1m in dB	89
max SPL 1m in dB	101	frequency response in Hz	94 - 20K
main construction material	ABS plastic	grille main material	steel
IP rating	40	Horizontal dispersion angle 1000 Hz	180°
Vertical dispersion angle 1000 Hz	180°	closest RAL colour (subject to deviations)	RAL9016 (W) / RAL9011 (BL)
Net weight product (kg)	0,97		


## POLAR PLOTS



MORE PICTURES



ACCESSORIES



**LRAPRE-BL**

Premium light rail adaptor KUBO3/5,SDQ5P,OVO5, pack of 2



**LRABAS-BL**

Basic light rail adaptor KUBO3/5, SDQ5P, OVO5, pack of 10



**LRABAS-BL**

Basic light rail adaptor KUBO3/5, SDQ5P, OVO5, pack of 10