


F-S

Non-Replaceable Probe - Epoxy Mount

Product Family: F-S



Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 2.00 (57.00) - 6.00 (170.00) - Stainless Steel, Gold plated

Mechanical:

Test Center (mil): 125

Test Center (mm): 3.18

Overall Length (mil): 780

Overall Length (mm): 19.81

Full Travel (mil): 100

Full Travel (mm): 2.54

Recommended Travel (mil): 66

Recommended Travel (mm): 1.68

Rec. Mounting Hole Size (mil): 86

Rec. Mounting Hole Size (mm): 2.18

Recommended Drill Size: #44

Thermal:

Max Operating Temp (°C): 150

Min Operating Temp (°C): -55

Electrical:

Current Rating (Amps): 5

Average DC Resistance lower than (mOhm): 30

Materials & Finishes:

Plunger Material: Heat-treated BeCu Gold plated or heat-treated Brass, Rhodium plated

Barrel Material: Brass, Gold plated


Ball Material: Stainless Steel, Gold plated

TIPS:


Tip Materials: BeCu, Alloy

Tips:

F-S-C



F-S-R



F-S-W

