


A-A-S

Non-Replaceable Probe - Epoxy Mount

Product Family: A-A-S



Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 0.50 (14.00) - 2.00 (57.00) - Stainless Steel, Gold plated

Mechanical:

Test Center (mil): 39

Test Center (mm): 1.00

Overall Length (mil): 310

Overall Length (mm): 7.87

Full Travel (mil): 30

Full Travel (mm): 0.76

Recommended Travel (mil): 20

Recommended Travel (mm): 0.51

Rec. Mounting Hole Size (mil): 31.5

Rec. Mounting Hole Size (mm): 0.80

Recommended Drill Size: #68 or 0.79 mm

Thermal:

Max Operating Temp (°C): 150

Min Operating Temp (°C): -55

Electrical:

Current Rating (Amps): 2

Average DC Resistance lower than (mOhm): 30

Materials & Finishes:

Plunger Material: Heat-treated BeCu, Gold plated

Barrel Material: Phosphor Bronze, Gold plated


Ball Material: Stainless Steel, Gold plated

TIPS:

Tip Materials: BeCu

Tips:

A-A-S-C



A-A-S-R

