

EDIFIER®

R1280DB

Studio Bookshelf Speaker

Equipped with dual RCA inputs the Studio 1280DB can produce up to 42W RMS of audio output. A 4 inch bass driver and front facing bass reflex port ensures bass notes are robust and rich in sound. Connect to multiple devices and personalize your listening experience with the bass and treble adjustment dials located on the active speaker. A remote control also controls the volume and mute function.



42
watts
R.M.S.
TOTAL POWER OUTPUT



Features

- Active bookshelf speaker system with 42W total power output
- Supports Bluetooth, Optical, Coaxial and Dual RCA inputs
- Bass, treble and master volume dials located on the side panel
- Wireless remote control for volume adjustment and mute
- Calibrated, flared front-facing bass reflect port
- 100% MDF wooden enclosures to minimize acoustic resonance

Specifications

Power output	: L/R: 21W+21W RMS
Signal to noise ratio	: ≥85dBA (A)
Noise level	: ≤25dB (A)
Input sensitivity	: LINE IN1: R/L:450±50mV LINE IN2: R/L:550±50mV OPT/COA: R/L:500±50mFFS Bluetooth: R/L:700±50mFFS
Frequency response	: 55Hz-20KHz
Bass unit	: 4 inch (116mm)
Tweeter unit	: Ø13mm silk dome tweeter
EAN code	: 6923520265527



Disclaimer: All specifications are subject to change without notice

www.edifier.com

A Passion for Sound