

EDIFIER®

R1700BT

Multifunctional speakers for your everyday needs

The R1700BT is a powerful studio speaker set with an edgy design. It produces 66W RMS from the 4 inch bass driver and 19mm tweeter driver in each speaker. A front facing bass reflex port emphasizes lower frequencies, allowing for richer bass performance.

The R1700BT incorporates Digital Signal Processing (DSP) and Dynamic Range Control (DRC) to prevent distortion levels even at the highest volumes, producing crisp, clean audio.



66
watts
R.M.S
TOTAL POWER OUTPUT



Features

- Active bookshelf speaker system
- Bluetooth pairing capability for music playback
- Dual RCA inputs for connectivity to multiple audio sources
- Class D amplifier system with Digital Signal Processing (DSP) and Dynamic Range Control (DRC)
- 100% MDF wooden enclosures to minimize acoustic resonance
- Universal 100V-240V power supply

Specifications

Power Output	: RMS 15W x 2 + 18W x 2 (DRC on)
Signal to noise ratio	: ≥85dBA
Frequency response	: 60Hz ~ 20KHz (@+/-6db)
Input sensitivity	: PC:700±50mV, AUX:550±50mV
Input type	: PC, Auxilliary
Bass driver	: 4 inch (119mm), 6Ω
Treble driver	: Φ19mm, Silk dome tweeter, 6Ω
EAN code	: 6923520265091 (UK)



Bluetooth™



Disclaimer: All specifications are subject to change without notice

www.edifier.com

A Passion for Sound