

Order symbol: ARK1086CHLM
Product nbr: 8561474
Description: PC Enclosure
Remarks: Hinged opaque cover w/Plastic quick release latch. Base includes 1/2 and 3/4 inch knock-outs and metal mounting feet

EAN: 6418074096500
El. number:
Finland:

Including: Hinged cover. Base with 10-32 brass inserts, latched cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:		Length	Width	Height	Accessories:	
mm:		254	203	152	ALBP108	Aluminum Back Panel
inch:		10.0	8.0	6.0	ADFP108	Dead Front Panel w/ screws
					ASP108	Aluminum Swing Panel
					ASPK108	Swing Panel Kit incl. Panel
					ASPHK10	Swing Panel Kit w/o Panel
					AMFL8	8" Mounting Flange Set
Materials:					Rating:	
Material:	Polycarbonate					
Base colour:	RAL 7035 -light grey					
Cover screws material:	Stainless steel					
Cover colour:	RAL 7035 -light grey					
Gasket material:	Polyurethane					
Temperatures:						
Temperature °C (short term):	-40 ... 140 °C				Ingress Protection (EN 60529): IP66/IP67	
Temperature °C (continuous):	-40 ... 80 °C				Impact Resistance (EN 62262): IK09	
Temperature °F (short term):	-40 ... 284 °F				Electrical insulation: Totally insulated	
Temperature °F (continuous):	-40 ... 175 °F				Halogen free (DIN/VDE 0472, Part 815): 1	
Accessories:					UV resistance: UL 508	
					Flammability Rating: UL 508	
					Glow Wire Test (IEC 695-2-1) °C: 960	
					NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	
ABP108		Painted Steel Back Panel				

