

# SHAVER SOCKETS

Traditional single and double gang dual voltage shaver sockets suitable for bathroom use.

- One shot thermal protection
- Accepts British and Continental plugs
- Auto switching shutters - prevents two plugs being inserted at the same time



	SHAS	P17	P17C	P17SC	HS1
<b>Product Finish</b>	White	White	Chrome	Chrome	White
<b>Description</b>	Double Gang Shaver Socket - curved front face	Double Gang Shaver Socket - Flat front face	Double Gang Shaver Socket - Flat front face	Double Gang Shaver Socket - Flat front face	Single Gang Shaver Socket with standard white front plate
<b>Product Dimensions</b>	H146 x W85 x D49mm	H148 x W87 x D49mm	H147 x W88 x D49mm	H147 x W88 x D49mm	H86 x W86 x D73mm
<b>Product weight</b>	613 gms	620 gms	675 gms	675 gms	218 gms
<b>Barcode</b>	5012739605024	5012739610417	5012739610431	5012739610424	5012739620874
<b>IP Rating</b>	IP41	IP41	IP41	IP41	IP41
<b>Voltage</b>	230V ~ 115/230V ~	230V ~ 115/230V ~	230V ~ 115/230V ~	230V ~ 115/230V ~	230V ~ 115/230V ~
<b>Pack Quantity</b>	1	1	1	1	1
<b>Guarantee</b>	1 Year	1 Year	1 Year	1 Year	1 Year
<b>Main housing material</b>	High gloss thermoplastic	Scratch Resistant Urea	Steel	Steel	High gloss thermoplastic
<b>Certification &amp; Conformity</b>	BS EN 61558-1 & BS EN 61558-2-5	BS EN 61558-1 & BS EN 61558-2-5	BS EN 61558-1 & BS EN 61558-2-5	BS EN 61558-1 & BS EN 61558-2-5	BS EN 61558-1 & BS EN 61558-2-5