


Mod. 5218 B

COPOLYMER POLYPROPYLENE WATERPROOF CASE



Metric mm-Kg-C°



INTERNAL DIMENSIONS

L Length	520 mm
W Width	285 mm
D Depth	180 mm
Lid	30 mm
Base	150 mm


EXTERNAL DIMENSIONS

L Length	550 mm
W Width	350 mm
D Depth	200 mm

OTHER DATA

Weight empty	3.75 Kg
Weight with foam	4.30 Kg
Weight with custom foam	Kg
Volume	26.6 lt
Buoyancy	20 Kg/max
Operating temperature	°C min -33 / max +90

Imperial in-lbs-F°



INTERNAL DIMENSIONS

L Length	20 1/2 in
W Width	11 1/4 in
D Depth	7 1/16 in
Lid	1 3/16 in
Base	5 7/8 in

EXTERNAL DIMENSIONS

L Length	21 5/8 in
W Width	13 3/4 in
D Depth	7 7/8 in

OTHER DATA

Weight empty	8.26 lbs
Weight with foam	9.47 lbs
Weight with custom foam	lbs
Volume	7.02 gal
Buoyancy	44.09 lbs/max
Operating temperature	°F min -27.4 / max +194