



NT 30/1 TACT TE H *GB 240V

With a guaranteed filtration efficiency of 99.995%, the 30/1 Tact Te H wet and dry vacuum cleaner is the first choice for removing dusts hazardous to health in dust class H.



NT 30/1 TACT TE H *GB 240V

Technical data

Order Number	1.148-257.0	
EAN code	4054278483672	
Air flow	l/s	74
Vacuum	mbar / kPa	254 / 25,4
Container capacity	l	30
Max. rated input power	W	1380
Standard nominal size	35	
Sound level	dB(A)	69
Weight	kg	14,4
Dimensions (L x W x H)	mm	560 × 370 × 580


Equipment

Suction hose	m	4	Caster with brake	■
Filter bag		Fleece	Filter cleaning	Tact Filter Clean
Wet and dry floor tool	mm	360		
Crevice nozzle		■		
Connector for electric tools		■		
Automatic on/off control for electric power tools		■		
Antistatic system		■		
Eco filter system		■		
Flat pleated filter		Fibreglass		
Sturdy bumper		■		
Safety class		I		

■ Included in delivery.

ACCESSORIES FOR NT 30/1 TACT TE H *GB 240V 1.148-257.0

KÄRCHER



		Order Number	Quantity	ID	Length	Width	Price	Description	
Plastic bend									
Elbow complete packaged NW35 2K	1	2.889-168.0	1 piece(s)	ID 35					<input checked="" type="checkbox"/>
Elbow packaged NW35 2K	2	2.889-170.0	1 piece(s)	ID 35					<input type="checkbox"/>
All-purpose nozzles (wet/dry)									
Floor tool packaged NW35 360mm	3	2.889-152.0	1 piece(s)	ID 35		360 mm			<input checked="" type="checkbox"/>
Crevice nozzles									
Crevice nozzle wet and dry packaged NW35	4	2.889-159.0	1 piece(s)	ID 35	225 mm				<input checked="" type="checkbox"/>
Suction tubes stainless steel									
Set suction tube stainless steel NW35 55	5	2.889-192.0	1 piece(s)	ID 35	550 mm				<input checked="" type="checkbox"/>
Set suction tube stainless steel NW40 55	6	2.889-194.0	1 piece(s)	ID 40	550 mm				<input type="checkbox"/>
Suction tube, ID 40	7	6.902-081.0	1 piece(s)	ID 40	0,5 m			Stainless steel suction tube (DN 40, 0.5 m) only suitable for NT vacuum cleaners.	<input type="checkbox"/>
Suction hoses complete (Clip-system)									
Hose electrically conducting packaged NW	8	2.889-137.0	1 piece(s)	ID 35	4 m				<input checked="" type="checkbox"/>
	9	2.889-136.0	1 piece(s)	ID 35	2,5 m				<input type="checkbox"/>
	10	2.889-161.0	1 piece(s)	ID 35	2 m				<input type="checkbox"/>
Adapter for electric power tools, clip on, el.									
Sleeve electrically conducting packaged	11	2.889-151.0	1 piece(s)	ID 35					<input checked="" type="checkbox"/>
HEPA filter for dust class H									
HEPA surface filter	12	6.904-242.0	1 piece(s)					HEPA surface filter - dust class H (HEPA 13) - with glass-fibre layers increases filter capacity when vacuuming health-endangering and carcinogenic dust.	<input type="checkbox"/>
Plastic sacks for dust-free disposal									
Disposal bag 10-parts PE	13	2.889-158.0	10 piece(s)						<input type="checkbox"/>
Car cleaning nozzles									
Car nozzle DN35	14	6.906-108.0	1 piece(s)	ID 35		90 mm		Angled, flat, plastic car vacuuming tool with about 90 mm working width. Only for NT vacuum cleaners.	<input type="checkbox"/>
Other									
Drilling dust tool	15	2.679-000.0	1 piece(s)						<input type="checkbox"/>

■ Included in delivery. □ Available accessories.