


6" USB A Male to Micro B Male Cable



Diagram



Dimensions : Millimetres

Note:

- Cable Specifications: 28AWG (7*0.12Cu)*1P+28AWG (7/0.12Cu)*2C+AD(7/0.12CCAM)+Braid (16*3/0.12ALMG)
Jacket Material: PVC OD: 3.8mm \pm 0.15mm

Cable Colour: Black

Cable Printing: USB 2.0 Cable Fully Rated 80°C 30V

- Connector A: USB A Male Solder Type USB 2.0 Compliant
Insulation: White
Contact: Gold Plated
Shell: Nickel Plated
- Connector B: USB B Male Solder Type
Insulation: Black
Contact: Gold Plated
Shell: Nickel Plated
- Over Mold: PVC-BLACK
- Parameter Settings: Conductive Resistance: 3 Ω
Insulation Resistance: 5M Ω (Min.)
- 100% electrical performance test

Part Number Table

Description	Part Number
6" USB A Male to Micro B Male Cable	83-16410