

3.5mm x 70mm Cobalt Ground Jobber Drill Pack of 2

Code	GCJT035
Size (Dia)	3.5mm
Overall Length	70mm
Cutting Angle	135 Degree Split Point
Pack Qty	2
Packaging	Plastic Blister on Card
Weight	16g
Barcode	5039197071680



Description

Professional quality, fully ground 5% (M35) Cobalt drill bits
M35 (5% Cobalt) High Speed Steel increases Heat and Wear Resistance
For drilling very hard, dense metals such as stainless steels, high tensile steels and cast iron.
135° Split Point Tip for easy drill start without Skidding
Manufactured to DIN338 standard

Applications

For drilling high tensile steels, stainless steel, steel, cast iron and other "Tough to Drill" metals
Always use Cutting oil / spray when drilling metals

Suitable For

For use with all makes of pillar drills, mains powered and cordless rotary drills.