

Part number


# PE 3263 SV



## Brief description:

hoods, plugs, 2 poles + PE, 32 (A.C.), 200 ÷ 250V, 6 blue, straight, IP44

### Product description

<b>Model</b>	plugs
<b>Version</b>	PLUSO, plugs and socket-outlets
<b>Series</b>	PE...SV
<b>Product type</b>	coupler
<b>Style</b>	straight
<b>Family</b>	plugs and socket-outlets
<b>N. of poles</b>	2 poles + 
<b>Clock position</b>	6

### Technical data

<b>Current</b>	32 A (A.C.)
<b>Voltage</b>	200 ÷ 250 V
<b>Frequency</b>	50 and 60 Hz.
<b>Operating temperature range (min, max)</b>	-40°C ... +125°C
<b>Material</b>	thermoplastic
<b>IP degree of protection</b>	IP44

### Further technical details

<b>Weight</b>	212,00 g
---------------	----------

### Approvals / Standards

<b>Reference standard</b>	EN 60309-1 and -2
<b>Quality mark</b>	 , EAC

### General ordering information

<b>EAN13 code</b>	8015747067270
-------------------	---------------

### Packaging Information

<b>Packaging length</b>	190,00 mm
<b>Packaging height</b>	170,00 mm
<b>Packaging width</b>	285,00 mm
<b>Packaging weight</b>	2,12 kg
<b>Packaging volume</b>	9,21 dm <sup>3</sup>
<b>Packaging description</b>	Carton box
<b>Packaging quantity</b>	10 Pcs
<b>Packaging EAN code</b>	8015747067287


Part number

# PE 3263 SV



Catalogue drawings

(16 / 32A) PE ... SV



PE ... SV	A	B	Ø min	Ø max	
<b>16A</b> 2P+⊕	143,5	59	7	17	
	3P+⊕	148,5	66	7	17
	3P+N+⊕	167,5	75	9	22
<b>32A</b> 2P+⊕	187	80	9	22	
	3P+⊕	187	80	9	22
	3P+N+⊕	192,5	87	9	22