

## Specification Sheet

Part Number: 156-00539



Cable Tie & Edge Clip, 8.0" Long, EC4A, 1–3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg

Article Number	156-00539
Type	T50REC4A
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>• Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.</li><li>• Edge Clip provides low insertion force and high extraction force ideal for assembly environments.</li><li>• Two piece assembly allows the mount to slide along the strap ensuring proper orientation.</li></ul>
Quantity Per	bag

### Product Description

The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

**Short Description**

Cable Tie &amp; Edge Clip, 8.0" Long, EC4A, 1–3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg

**Global Part Name**

T50REC4A-PA66HS/PA66HIRHS-BK

**Minimum Tensile Strength (Imperial)**

50.0

**Minimum Tensile Strength (Metric)**

225

**Length L (Imperial)**

8.0

**Length L (Metric)**

202.0

**Fixation Method**

EdgeClip, top, assembled, 2 piece

**Identification Plate Position**

none

**Releasable Closure**

No

**Variant**

Inside Serrated

**Width W (Imperial)**

0.18

**Width W (Metric)**

4.6

**Bundle Diameter Min (Imperial)**

0.20

**Bundle Diameter Min (Metric)**

5.0

**Bundle Diameter Max (Imperial)**

2.0

**Bundle Diameter Max (Metric)**

50.0

<b>Thickness T (Imperial)</b>	0.05
<b>Thickness T (Metric)</b>	1.2
<b>Height H (Imperial)</b>	0.05
<b>Height H (Metric)</b>	1.20
<b>Panel Thickness Min(Imperial)</b>	0.04
<b>Panel Thickness Max(Imperial)</b>	0.12
<b>Panel Thickness Min (Metric)</b>	1.0
<b>Panel Thickness Max (Metric)</b>	3.0
<b>Material</b>	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
<b>Material Shortcut</b>	PA66HIRHS PA66HS
<b>Material Cable Tie</b>	Polyamide 6.6 heat stabilized (PA66HS)
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +221°F (-40°C to +105°C) -40°F to +230°F (-40°C to +110°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	500

**Package Quantity (Metric)**

500

**Customs Number**

3926909987

**Weight (Metric)**

4.5