

F204 B-40/0,3



F204 B-40/0,3 Residual Current Circuit Breaker



General Information

| | |
|-----------------------|---|
| Extended Product Type | F204 B-40/0,3 |
| Product ID | 2CSF204592R3400 |
| EAN | 8012542358138 |
| Catalog Description | F204 B-40/0,3 Residual Current Circuit Breaker |
| Long Description | The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications. This product is particularly suitable for the protection against smooth d.c. earth fault currents. |

Ordering

| | |
|------------------------|----------|
| Minimum Order Quantity | 1 piece |
| Customs Tariff Number | 85363030 |

Popular Downloads

| | |
|-----------------------------------|-----------------------------|
| Data Sheet, Technical Information | 9AKK107046A0424 |
| Instructions and Manuals | Manual sheet inside the box |

Dimensions

| | |
|----------------------------|----------|
| Product Net Width | 0.072 m |
| Product Net Height | 0.085 m |
| Product Net Depth / Length | 0.069 m |
| Product Net Weight | 0.380 kg |

Technical

| | |
|-------------------------------|---|
| Standards | IEC/EN 61008 |
| Operating Characteristic | Instantaneous |
| Type of Residual Current | B type |
| Rated Residual Current | 300 mA |
| Rated Current (I_n) | 40 A |
| Number of Poles | 4 |
| Position of Neutral Terminals | Right |
| Power Loss | at Rated Operating Conditions per Pole 1.81 W |

Environmental

| | |
|-------------------------|--|
| Ambient Air Temperature | Operation -25 ... +55 °C Storage -40 ... +70 °C |
| RoHS Status | Following EU Directive 2011/65/EU |

Certificates and Declarations (Document Number)

| | |
|--------------------------------|-----------------------------|
| Declaration of Conformity - CE | 9AKK106713A5602 |
| Environmental Information | Refer to RoHS |
| Instructions and Manuals | Manual sheet inside the box |
| RoHS Information | 2CSC423001K2702 |

Container Information

| | |
|--------------------------------|---------------|
| Package Level 1 Units | 1 piece |
| Package Level 1 Width | 0.073 m |
| Package Level 1 Height | 0.078 m |
| Package Level 1 Depth / Length | 0.09 m |
| Package Level 1 Gross Weight | 0.525 kg |
| Package Level 1 EAN | 8012542358138 |

Classifications

| | |
|----------------------------|--|
| Object Classification Code | Q |
| E-nummer | 2160021 |
| ETIM 4 | EC000003 - Residual current circuit breaker (RCCB) |
| ETIM 5 | EC000003 - Residual current circuit breaker (RCCB) |
| ETIM 6 | EC000003 - Residual current circuit breaker (RCCB) |
| ETIM 7 | EC000003 - Residual current circuit breaker (RCCB) |

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCCBs → Residual Current Devices RCCBs

