

# ROLINE HQ VGA Cable + Ferrite, HD15, M/M, 15.0 m

<b>Product No.</b>	11.04.5265
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	11.04.5265
<b>EAN (single piece)</b>	7611990125487



- High quality cable for connection of a monitor to a graphics card or VGA splitter or amplifier
- As monitor connection cable with two additional ferrite cores
- 3 coax lines for the RGB signals and 7 AWG28 wires
- Connector casings moulded
- Double screened cable (braided and foil shield)
- Hand locking screws

## Technical specifications

Manufacturer	ROLINE
Product group	Cable
Product type	VGA Cables
Colour	black
Length	15 m
side 1 connector	D-Sub HD 15 Male
side 2 connector	D-Sub HD 15 Male
Side 1 Connector Type	HD D-Sub 15-pin (HD-15), VGA
Side 1 Connector Gender	Male
Side 2 Connector Type	HD D-Sub 15-pin (HD-15), VGA

---

Side 2 Connector Gender	Male
Area of application	External
Cable shielding	Double screened
Hand locking screws	Yes
Cable composition	3 Coax RGB 7xAWG28
Technical particularity	with ferrite