


Sockets

BU 10



Product	BU 10
description	Bright metal 4 mm diameter nickel-plated brass socket with solder connection and M6 thread. For installation in equipment chassis and switch panels till 11 mm wall thickness.
operating instruction	BA403
Articlenummer	930147000 Ni
drawing	
	
technical data	
connection	M6 thread, solder connection
rated voltage ⁽¹⁾	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽³⁾
rated current ⁽¹⁾ (consider derating curve)	16 A
material socket	brass, nickel plated
temperature range acc. To IEC61010 ⁽²⁾	-25 °C to +100 °C
inflammability class acc. to UL 94 (only valid for basic material of housing)	HB
standard	IEC 61010

4 mm system

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges

⁽³⁾ Other circuits that are not directly connected to mains

stand: 12.09.2018