



**Part Number:** 73744

277 VOLT BREAKER LOCKOUT



### Product Highlights

Risk Type: Electrical Risk  
Circuit Breaker Lockout Type: Single-Pole  
Voltage: 120/277 V  
Dimensions: 2.205 in H x 0.95 in W x 0.65 in D

### Overview

Clamp-on breaker lockouts are versatile and easy to install using the proprietary thumbwheel design - no screwdrivers needed!

- Extremely versatile - works on a wide range of single-pole and internal-trip multi-pole breakers
- Detachable cleat (included) expands the range of applicable breakers
- Equipping your employees with the proper lockout tools and warning devices can save lives, reduce lost employee time, and cut insurance costs
- Brady® is a world leader in lockout/tagout products and services offering industry expertise and a broad range of durable, easy-to-use lockout devices

## Specifications

Country of Origin	MX - All trade information (i.e. Country of Origin, Harmonized Schedule code, and/or Export Control Classification Number) and related assistance provided by Brady Corporation and its affiliates is provided for informational purposes only and is subject to change without notice. Any use of such information by you is without recourse to Brady Corporation or its affiliates and is at your own risk. This information is not provided as legal advice or as a substitute for obtaining specific legal advice. If you have any questions regarding your specific situation, you should consult your attorney.
Circuit Breaker Lockout Type	Single-Pole
Dimensions	2.205 in H x 0.95 in W x 0.65 in D
UOM	Each
Handle/Toggle Width	0.445 in
Maximum Shackle Diameter	0.31 in
Product Number	73744
UPC	754473737443
UNSPSC	39121901
Voltage	120/277 V
Color	Red
Includes	Cleat
Material	Polypropylene
Risk Type	Electrical Risk