

PRODUCT Data	
HARVARD MODEL NO	GPS06BLK
PRODUCT DESCRIPTION	Portable CD/FM Boombox
PRODUCT CATEGORY	AUDIO
COLOUR	BLACK
COUNTRY OF ORIGIN	CHINA
BARCODES (EAN-ITF)	5018379112014
	05018379112021

PRODUCT Specification
 TOP LOADING CD/CD-R/CD-RW PLAYER
 AM/FM RADIO (ANALOGUE TUNING)
 PLASTIC SPEAKER GRILLE
 TELESCOPIC FM ANTENNA
 LED DISPLAY FOR CD FUNCTION
 20-TRACK PROGRAMMABLE MEORY
 AUX-IN
 OUTPUT 2 X 1.2W
 AC/DC OPERATION


PRODUCT Technical Specification			
POWER OUTPUT	2 x 1.2w	MAINS / BATTERY	AC/DC
DISPLAY TYPE	LED	BATTERY	
DAB (Y/N)	N	TYPE UNIT	C6 x 6
BLUETOOTH	N	TYPE RC	N
MEDIA TYPE	as above		
EQ	N	CONNECTIONS	
HEADPHONE SOCKET	Y	TYPE	3.35mm JACK
CLOCK FUNCTION	N		
ALARM FUNCTION	N		

PRODUCT Features & Benefits
 Small compact deisgn
 Simple functionality
 Light weight for easy transit
 AC/DC for static or portable use

ACCESSORIES (Whats in the box)
 IB (one language)
 QSG
 Safety & guarantee booklet
 AC mains cable



DIMENSIONS				LENGTH (CM)	WIDTH (CM)	HEIGHT (CM)	NET WEIGHT (KG)	GROSS WEIGHT (KG)		
DISTRIBUTION FILL (@ 1.5M)		CONTAINER FILL		UNIT DIMS						
UNITS PER CARTON				PACKING INFORMATION						
TI	4	8	20' FCL	3044	UNIT	19.00	23.00	11.00	N/A	1.16
HI	4	4	40' FCL	6304	GIFT BOX	23.50	13.20	25.80	N/A	1.49
PALLET	128	4	40' HQ FCL	7392	SHIPPER CARTON	51.40	27.00	29.00	5.60	7.42



WASTE PACKING INFORMATION																	
TOTAL PER SHIPPER CARTON	<table border="1"> <tr> <td>PAPER</td> <td></td> <td>STEEL</td> <td></td> </tr> <tr> <td>GLASS</td> <td></td> <td>PLASTIC</td> <td></td> </tr> <tr> <td>METAL</td> <td></td> <td>WOOD</td> <td></td> </tr> <tr> <td>ALUMINIUM</td> <td></td> <td>OTHER</td> <td></td> </tr> </table>	PAPER		STEEL		GLASS		PLASTIC		METAL		WOOD		ALUMINIUM		OTHER	
PAPER		STEEL															
GLASS		PLASTIC															
METAL		WOOD															
ALUMINIUM		OTHER															

details are correct at time of print and subject to change