



<p>Fully mating connector, shatter-proof, flexible insulated sleeve. The tapering sleeve end also serves as kinking protection for the lead. Solder connection up to maximum cable cross-section of 2.5 mm². Nickel-plated brass contact material.</p>	<p>Fully mating connector, shatter-proof, flexible insulated sleeve with transverse hole. The tapering sleeve end also serves as kinking protection for the lead. Screw connection up to maximum cable cross-section of 1.5 mm². Nickel-plated brass contact material.</p>	<p>Fully mating connector, shatter-proof, flexible insulated sleeve with transverse hole. The tapering sleeve end also serves as kinking protection for the lead. Solder connection up to maximum cable cross-section of 2.5 mm². Nickel-plated brass contact material.</p>
<p>VON 30 rot/red</p>	<p>VQ 20 rot/red</p>	<p>VQ 30 rot/red</p>
<p>930 047-101</p>	<p>930 058-101</p>	<p>930 061-101</p>
<p>4 mm System</p>	<p>4 mm System</p>	<p>4 mm System</p>
<p>red</p>	<p>red</p>	<p>red</p>
<p>black color, order no. 930 047-100; blue color, order no. 930 047-102; yellow color, order no. 930 047-103; green color, order no. 930 047-104</p>	<p>black color, order no. 930 058-100; blue color, order no. 930 058-102; yellow color, order no. 930 058-103; green color, order no. 930 058-104</p>	<p>black color, order no. 930 061-100; blue color, order no. 930 061-102; yellow color, order no. 930 061-103; green color, order no. 930 061-104</p>
<p>4 mm</p>	<p>4 mm</p>	<p>4 mm</p>
<p>pin (spring-loaded)</p>	<p>pin (spring-loaded)</p>	<p>pin (spring-loaded)</p>
<p>solder</p>	<p>screw</p>	<p>solder</p>
<p>DC 60 V</p>	<p>DC 60 V</p>	<p>DC 60 V</p>
<p>30 A</p>	<p>16 A</p>	<p>30 A</p>
<p>3 mOhm</p>	<p>3 mOhm</p>	<p>3 mOhm</p>
<p>brass</p>	<p>brass</p>	<p>brass</p>
<p>nickel-plated</p>	<p>nickel-plated</p>	<p>nickel-plated</p>
<p>PVC-P</p>	<p>PVC-P</p>	<p>PVC-P</p>
<p>-25 °C to +70 °C</p>	<p>-25 °C to +70 °C</p>	<p>-25 °C to +70 °C</p>
<p>94 V-2</p>	<p>94 V-2</p>	<p>94 V-2</p>