

Connectable conductors

Clamping range, max.	6 mm ²
fine-stranded, min. H05(07) V-U	0,5 mm ²
fine-stranded, max. H05(07) V-U	4 mm ²
Solid, min. H05(07) V-U	0,5 mm ²
Solid, max. H05(07) V-U	6 mm ²
AWG, min.	26
AWG, max.	12
w. plastic collar ferrule, DIN 46228 pt 4, min.	0,5 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, max.	2,5 mm ²
Wire end ferrule , DIN 46 228/1, min.	0,5 mm ²
Wire end ferrule , DIN 46 228/1, max.	2,5 mm ²
Gauge to EN 60999 a x b; ø	2.8 mm x 2.4 mm; 3.0 mm
Clamping range, min.	0,13 mm ²

Approvals

Approvals



Classifications

ETIM 2.0	NK
eClass 4.1	NK
eClass 5.0	NK
eClass 5.1	NK

General ordering data

Order No.	1640870000
Short text for material	LP1N5.00/2 3.2 OR
EAN	4008190449957

- Additional colours on request
- Rated current related to rated cross-section and min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228 pt 1
- Wire end ferrule with plastic collar to DIN 46228 pt 4
- P on drg. = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

Related products

Order No.	Short text for material	Number of poles
1640880000	LP1N5.00/3 3.2 OR	3